

# LASER TATTOO REMOVAL MACHINE WITH AIR COOLER HEAD

## ND-YAG PRO X DISPLAY





## UNIQUE DESIGN



• Air cooler head -For cooling the epidermis to reduce pain and skin damage;

755nm

755nm

- **1064nm head** -For black, blue, brown tattoo and pigmentation removal;
- **532nm head** -For red, orange, pink and colorful tattoo and pigmentation removal;
- 1320nm head -For laser carbon peeling;

532nm

1064nm

1320nm

• **755nm head** -For spots removal, freckle removal, skin whitening and skin rejuvenation.

Unique Design Air Cooling Head for Skin Cooling During Treatment.

# **EXCLUSIVE ANDROID SYSTEM**

#### dermatech-ar medical and aesthetical treatments, school and supply

Android operation system creates an intelligent platform that is very helpful and friendly for device distributors and chain of beauty salon operators. It supplies many unbelievable functions for the Nd:YAG laser tattoo removal device in the 5G era.

1. The system provides main functions such as user management, video, voice, language, pictures, files, software version update, Internet access etc.;

2. The system provides CRM functions such as user data establishment, storage, analysis, transmission, and multi-device sharing and interconnection;

3. The system can realize the IoT functions such as the interconnection of wireless devices, portable devices and smart home appliances;

4. The system can realize free online remote system one-button upgrade, and online real-time push system updating;

5. The system can realize online self-inspection push to bring foolproof and convenient after-sales and maintenance service.



### **KEY ACCESSORIES**





#### **UK Xenon Lamp**

Ensure more powerful energy and longer lifetime.



#### **Special Laser Rod**

A special lens integrated in its inside for smaller size but stronger power. The laser beam calibration is not necessary after xenon lamp replacement.



#### **New Design Treatment Handle**

Used for long hours usage, greatly reducing operator fatigue.



**Japan Imported Capacitor** Powerful, fast and stable energy output.



**Pre-ignition Power Supply** 

Enables the machine to enter the working state in advance, energy 3% higher and life 5% longer than the one without pre-ignition function.



### EFFECT





### PARAMETER

### dermatech-group® medical and aesthetical treatments, school and supply

### **Technical Parameters**

| Power               | 500W                            |
|---------------------|---------------------------------|
| Screen              | 13.3" OGS Android screen        |
| Wavelength          | 1064nm, 532nm, 1320nm and 755nm |
| Energy              | 10~2000mj                       |
| Frequency           | 1~10Hz                          |
| Spot Size           | 2~8mm                           |
| Laser Bars size     | φ5mm/φ6mm/φ7mm (Optional)       |
| Cooling Power       | 15W                             |
| Cooling Temperature | 5°C                             |
| N.W/G.W             | 20Kg/25Kg                       |
| Machine Size        | 50*48*30cm                      |
| Packing Size        | 60*51*41cm                      |
| Input Voltage       | AC220V, 50Hz/ AC110V, 60Hz      |

